

Blind sleeve - CES-LTPG-GY - 0801716

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Large blind sleeve, material: SEBS



Product description

Blind sleeves seal feed-through sections that are not required in CES sealing frames



Key commercial data

Packing unit	10 pc
GTIN	4 046356 675178
Weight per Piece (excluding packing)	34.03 g
Custom tariff number	85472000
Country of origin	Poland

Technical data

Dimensions

Conductor sealing range	(Blind sleeve)
-------------------------	----------------

Ambient conditions

Degree of protection	IP54
	IP65 (when using a CES-B...-SFFS-PLBK sealing frame with screw locking and a cone sleeve with cable binder)
Ambient temperature (operation)	-40 °C ... 80 °C (static)

General

Product description	Blind sleeves seal feed-through sections that are not required in CES sealing frames
Material	SEBS
Inflammability class according to UL 94	V0
Color	gray

Blind sleeve - CES-LTPG-GY - 0801716

Classifications

eCl@ss

eCl@ss 4.0	27081002
eCl@ss 4.1	27081002
eCl@ss 5.0	27081002
eCl@ss 5.1	27081002
eCl@ss 6.0	27081002
eCl@ss 7.0	27081002
eCl@ss 8.0	27081002

ETIM

ETIM 3.0	EC000879
ETIM 4.0	EC000451
ETIM 5.0	EC000451

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Approvals

Approvals


Approvals

UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals


Approvals submitted


Approval details

UL Recognized 

Blind sleeve - CES-LTPG-GY - 0801716


Approvals

cUL Recognized 

cULus Recognized 

Drawings

Dimensioned drawing



Dimensional drawing