



### Main

Range of product	PratiKa
Product or component type	Socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Industrial socket type	Fast
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

### Complementary

Mounting mode	Panel-mounted
Plug, socket, control station shape	Angled
[In] rated current	16 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Self-extinguishing engineering polymer housing:
Contacts material	Brass sleeves:
Connections - terminals	Fast connection
Cable cross section	1...2.5 mm <sup>2</sup>
Product weight	0.164 kg
Base dimension	65 x 85 mm
Height	85 mm
Width	65 mm
Depth	105 mm
Colour	Grey ( RAL 7035 )
Voltage colour	Red

### Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-1
Relative humidity	90 % ( 20 °C ) 70 % ( 30 °C ) 50 % ( 40 °C )
Ambient air temperature for operation	35 °C ( 86400 s )