

Specifications for BMP71 Label Printer Labels

Adhesive	Permanent Acrylic
Article No.	115089
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	White/Transparent
Finish	Matt
Order Reference	M71-23-427
Printable Area - Height (mm)	25.40
Printable Area - Width (mm)	25.40
Printer Compatibility	BMP71
Size - Height (mm)	101.60
Size - Width (mm)	25.40
Additional Information	Self-Laminating;Self-Extinguishing;Excellent water & oil resistance;Excellent abrasion and smudge resistance
Thickness (mm)	0.102
Total Qty per Pack	100 Label(s) / Box
Vertical Repeat (mm)	104.78
Wire Gauge	1-0000
Approval/Compliance	UL Recognised
Ribbon Series	M71-R4300
Application	Voice & Data Communication; Wire & Cable Marking
Industry	Aerospace;Data & Telecommunications;Defence;Electrical;Mass Transit
Description	Labels for the BMP™71 Label Printer. Please Note: This material is UL Approved with its respective ribbon. See the Recommended Ribbon Series for the appropriate ribbon to use.
Max. Characters per Line	24
Max. Lines of	10

Text	
Max. Service Temp. °C	60
Max. Wire/Cable Diameter (mm)	24.30
Min. Service Temp. °C	-80
Min. Wire/Cable Diameter (mm)	10.80
Shape	Rectangle
Surface	For smooth & textured/rough surfaces
Voice/Data Application	Communications Cables