

Cable - FLK 50-PA/EZ-DR/HF/KS/ 100/YUC - 2904739

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 1 m

Why buy this product

- Molded connectors
- KS/AKB-compatible connectors on the module side
- Can be screwed on
- Lateral cable outlet of the I/O module



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 882897 |
| Weight per Piece (excluding packing) | 312.5 g |
| Custom tariff number | 85444290 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

General

| | |
|---|---|
| Nominal voltage U_N | 30 V DC |
| Max. current carrying capacity per path | 500 mA (Up to 55°C ambient temperature) |
| Max. conductor resistance | 0.16 Ω /m |
| Length of cable | 1 m |
| Single wire, cross section | 0.14 mm ² |
| AWG | 26 |
| Conductor construction: Number of litz wires: | 7 |
| Single wire, material | Cu tin-plated |
| External diameter | 11 mm |
| Shielding | yes |

Cable - FLK 50-PA/EZ-DR/HF/KS/ 100/YUC - 2904739

Technical data

General

| | |
|--------------------------|-----------------------------------|
| Standards/specifications | Halogen-free sheath |
| | Flame retardancy |
| | No development of corrosive fumes |
| Outer sheath, material | PVC |
| External sheath, color | Gray RAL 7035 |

Environmental conditions

| | |
|---|------------------------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Flame resistance | IEC 60332-3 |
| Resistance to oil | DIN VDE 0472 Part 803, test type B |
| Gasoline resistance | Against occasional splashes |

Connector, module side

| | |
|---------------------|--------------------------------|
| Number of positions | 50 |
| Connectors | IDC/FLK socket strip (2.54 mm) |
| Number of plugs | 1 |

Connector, controller side

| | |
|---------------------|--------------------------------|
| Number of positions | 50 |
| Connectors | IDC/FLK socket strip (2.54 mm) |
| Number of plugs | 1 |

Connection data

| | |
|-------------------|------------------|
| Connection method | Screw connection |
| Torque | 0.5 Nm |

Supported controller

| | |
|---------------------|--------------------------|
| Controller | YOKOGAWA CENTUM CS3000R3 |
| - suitable I/O card | ADV151 |
| | ADV551 |
| Controller | YOKOGAWA STARDOM |
| - suitable I/O card | NFDV151 |
| | NFDV551 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |

Cable - FLK 50-PA/EZ-DR/HF/KS/ 100/YUC - 2904739

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 7.0 | 27141152 |
| eCl@ss 8.0 | 27249205 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000237 |
| ETIM 5.0 | EC000237 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11 | 39121409 |
| UNSPSC 12.01 | 39121409 |
| UNSPSC 13.2 | 39121409 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

| |
|-----|
| EAC |
|-----|

Accessories

Spare parts

Screw set - VF-SCREW-YOKOGAWA/M3X18/DCS - 2902873



Replacement screw M3x18 for Yokogawa system cable, front adapter control side.

Cable - FLK 50-PA/EZ-DR/HF/KS/ 100/YUC - 2904739

Accessories

Screw set - VF-SCREW-YOKOGAWA/M4X25/KS - 2902874



Replacement screw M4x25 for Yokogawa system cable, module side.

Drawings

Connection diagram

| 50-pos. connector to the I/O card | 50-pos. connector to the module | Wire color |
|---|---------------------------------------|---------------|
| 1 | 50 | black |
| 2 | 49 | brown |
| 3 | 48 | red |
| 4 | 47 | orange |
| 5 | 46 | yellow |
| 6 | 45 | green |
| 7 | 44 | blue |
| 8 | 43 | violet |
| 9 | 42 | gray |
| 10 | 41 | white |
| 11 | 40 | white-black |
| 12 | 39 | white-brown |
| 13 | 38 | white-red |
| 14 | 37 | white-orange |
| 15 | 36 | white-yellow |
| 16 | 35 | white-green |
| 17 | 34 | white-blue |
| 18 | 33 | white-violet |
| 19 | 32 | white-gray |
| 20 | 31 | brown-black |
| 21 | 30 | brown-red |
| 22 | 29 | brown-orange |
| 23 | 28 | brown-yellow |
| 24 | 27 | brown-green |
| 25 | 26 | brown-blue |
| 26 | 25 | brown-violet |
| 27 | 24 | brown-gray |
| 28 | 23 | brown-white |
| 29 | 22 | green-black |
| 30 | 21 | green-brown |
| 31 | 20 | green-red |
| 32 | 19 | green-orange |
| 33 | 18 | green-blue |
| 34 | 17 | green-violet |
| 35 | 16 | green-gray |
| 36 | 15 | green-white |
| 37 | 14 | yellow-black |
| 38 | 13 | yellow-brown |
| 39 | 12 | yellow-red |
| 40 | 11 | yellow-orange |
| 41 | 10 | yellow-blue |
| 42 | 9 | yellow-violet |
| 43 | 8 | yellow-gray |
| 44 | 7 | yellow-white |
| 45 | 6 | gray-black |
| 46 | 5 | gray-brown |
| 47 | 4 | gray-red |
| 48 | 3 | gray-orange |
| 49 | 2 | gray-yellow |
| 50 | 1 | gray-green |