

Datasheet

RS Pro Din Rail G, TS32 Slotted, 1000mm x 32mm x 15mm

RS Stock No: **467-393**



Product Details

RS Pro 11-way commoning block in clear colour, has a screw down termination for easy installation. This commoning block is designed for commoning together of same potential cables of 2 to 10 AWG. It is current rated for 170 A and voltage rated for 450 V. This terminal block is suitable for use in junction boxes, panel boards, equipotential earthing applications and where disconnection of branch wires must be possible without interruption on the main conductors. In this, each pole of the terminal is linked internally by a copper busbar, providing a low resistance connection path. It measures 58 x 43 x 42 mm.

Features and Benefits

- 11-way commoning block in clear colour
- Screw down termination
- Designed for commoning together of same potential cables of 2 to 10 AWG
- Current rated for 170 A
- Voltage rated for 450 V
- Suitable for use in junction boxes, panel boards, equipotential earthing applications



Specifications:

Compatibility	G
DIN Rail Type	TS32 Slotted
Height	15 mm
Length	1000 mm
Material	Steel
Width	32 mm