

Presence detector  
Busch-Watchdog Presence tech BasicLINE mini



For switching lighting systems that depend on brightness and movement.  
Detection range (installation height 3m, up to 6m in diameter).  
Low mounting height due to separate sensor/actuator concept.  
Continuously variable detection sensitivity.  
With brightness-independent test mode for evaluating the detection zone.  
With detection display in test mode.  
Ceiling installation using integrated spring bracket.  
Surveillance density: 19 sectors with 76 switching segments.  
Switch-off delay: approx. 1 sec - 15 min or short-time pulse adjustable.

Rated voltage: 230 V~, +10 % / -10 %, Rated frequency: 50 Hz, Power dissipation: 1.5 W,  
Outputs: 1 Normally open contact, potential-bound, Suitable for: 230 V incandescent lamps, Rated power: 2000 W, Suitable for: Energy-saving bulbs, Rated power: 7 - 400 W, Suitable for: Fluorescent lamps, Rated current: 4 AX, cos phi 0.5, Rated power: 1000 W/VA  
Protection class (Device): IP 20, Protection class (Sensor): IP 40, Temperature range (Device): 0 °C to 45 °C,  
Brightness limit value: 10 Lux - 1000 Lux -, Daytime operation, Detection angle: 360 °,  
Mounting depth: 77 mm, Mounting height: 2 m - 5 m,  
When mounting the actuator through the drilled hole of the sensor an installation depth of ? 205 mm is to be taken into account., In combination with a relay/contactors, an RC suppressor 6899 has to be used.

Order Code : 2CKA006800A2517  
Article No. : 6811 EB-500  
EAN: 4011395148037

