

Product Data Sheet



Schoeller Allibert

9567001456

R11052 GREEN 504 PE7



Classification

Main Product Group	Stack/Nest Containers
Product Group	Tellus

Measures (mm)

External Length at Top	600
External Width at Top	400
External Height	300
External Length at Bottom	0
External Width at Bottom	0
Internal Length at Top	460
Internal Width at Top	340
Internal Length at Bottom	460
Internal Width at Bottom	340
Usable Height	270
Height Stacking Rim	15
Stacking Height	
Total Height Nested	85
Nesting %	72

Miscellaneous

Customer Exclusive	
Drawing No	
Material	PE7
Temperature Range	-30°C to +30°C
Label Holder	
Type Base	Perforated
Type Longsides	Perforated
Type Shortsides	Perforated
Food Approved?	Y
UV Included?	
UV level	

Packaging

Units/package	540
Units/pallet	45
Pallet Volume (m3)	2.712
Pallet Length (mm)	1200
Pallet Width (mm)	1000
Pallet Height (mm)	1130

Weight & Volume

Net Weight (kg)	2.0
Usable Volume (l)	50

Performances

Unit Load Capacity	15
Max Static Stacking Load	200
Max Dynamic Stacking Load	

Doors Longside	No
Doors Shortside	No
Lid Available	LI104604
Handles	2 Short Side
Hand Grips Longside	
Hand Grips Shortside	Open
Drain Holes	