

## PLUG 6P+E IP66/IP67 32A 6h 346-415V AC






### TechData

Rated current	32A
Commercial series	OPTIMA-SEVEN Series
Poles	6P+E
Hour position	6h
Rated voltage	380-415V
Working frequency	50Hz
Working frequency	60Hz
Colour	RED
Syntetical description	PLUG
Protection degree	IP66/IP67
Types of available outlets	STRAIGHT

### Approvals and Certifications

**CE** CE  
Declaration of conformity

### Standards and Laws

-  EN 60309-1 (1999)  
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A1 (2007)  
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
-  EN 60309-1/A2 (2012)  
[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements

### Packaging

Description	Box
Quantity	10
Gross weight	3.56 KG
Volume	13260 CCM
Dimensions	255x325x160 (MM)