



3
 JAHRE
 YEARS
 GARANTIE
 WARRANTY

ANSMANN Torch Future 3D Plus

- High quality torch with a specially hardened surface and a waterproof housing for professional use
- Newest LED technology
- Very good thermo management and less energy waste
- Operating time approx. 40h
- Beam up to approx. 800m
- 160 Lumen / 8500 Lux
- Very handy surface, ideal for one-handed operation, even with glove
- Including 3x Mono D Alkaline Batteries
- More attractive packaging design with a higher quality

INFORMATION

Product name	Torch Future 3D Plus
Part No.	5816033
EAN-Code	4013674160334
Customs tariff number	85131000
Material Group	02
Product content	Torch, 3 Mono D batteries

Product	315 × 50 × 50 mm / 791 g
Packing + Product	134 × 60 × 385 mm / 862 g
Packing Unit	4 (390 × 280 × 120 mm)

