




KEYING LOCATION




(P/N 2-178288-4 ONLY)
(KEYING: Y)




(P/N 2-178288-3 ONLY)
(KEYING: Y)




(P/N 2-178288-6,-8)
(KEYING: Y)



(P/N 1-178288-4 ONLY)
(KEYING: X)



(P/N 1-178288-3 ONLY)
(KEYING: X)



(P/N 1-178288-5,-6,-7,-8)
(KEYING: X)

				Copyright ©1991 年 タイコ・エレクトロニクス・アンプ株式会社		Copyright ©1991 Tyco Electronics AMP K.K. ALL RIGHTS RESERVED.		 Tyco Electronics Corporation Kawasaki, Japan	
				適合電線径範囲(WIRE RANGE) mm ² AWG - >		被覆外径(INSULATION DIA.) - mm ϕ		名称(NAME) REC HSG FOR DYNAMIC,SINGLE ROW ダイナミックD-3100リセハウジング	
				材料(MATERIAL) SEE NOTE 法記参照		仕上(FINISH) —		一般公差 (GENERAL TOLERANCE) 10mm : ±0.2 10mm 30mm : ±0.25 30mm 100mm : ±0.3 角 度 : ±3°	
SEE 1 OF 2				DR.		DE. OF 2		SIZE A3	
				CHK.		APP.		LOC J	
LTR 変更 (REVISION RECORD)				DR		CHK		DATE	
				SEE				番号(No.) 178288	
								178288	
								R 度(SCALE) 2-1	
								REV. E3	
								SHEET 2 OF 2	