

60W Triac Dimmable Driver



Features:

- Triac dimmable
- Suitable for leading/ trailing edge dimming
- Constant current and constant voltage design
- Protections: Short circuit/ Overload/ Over voltage
- Built-in PFC function (PFC>0.95)
- Cooling by free air convection
- Up to 86% efficiency
- Fully isolated, delivering up to 60W of power



Model No.	ELED-60-24T
Input Voltage Range	220-240VAC
AC Frequency	50-60Hz
Output Mode	Constant Voltage
Output Current	0-2.0A
Output Voltage	24V
Output Power	60W Max
Power Factor	>0.95
Efficiency	>86%
Operating Temperature	-30°C-+45°C
Relative Humidity	5-95%
Isolation Voltage	In/ Out 3000VAC
Vibration	5-55Hz/ 2g, 30minutes
EMI	EN55015 Class B
Safety	EN61347-1, EN61347-2-13
Electromagnetic Immunity	EN61547, EN55024, EN61000-4-2, 3, 4, 6, 8, 11
Harmonic Current Emissions	EN61000-3-2, EN61000-3-3
Dimensions (mm)	170x 50x 31.5

Dimensions Chart(mm)

