

## Datasheet

# RS Pro 4m Extension Reel Type G - British, USB, 2+2 Socket, Unwound Current Rating 13A, 230 V ac, White

RS Stock No: **889-2507**



## Product Details

RS Pro NEMA rated L21 - 20P twist lock main plug is used for AC main electricity in N. America and other countries. This twist lock plug has a voltage rating of 120/208 V and is current rated for 20 A. The twist-lock plug guarantees a more reliable connection, where vibration or incidental impact could disconnect a normal plug. It has screw type terminal for easy installation. The plug is suitable for industrial and commercial applications.

## Features and Benefits

- Twist-Lock technology provides more reliability
- 22/30 A -250 V ac
- Insulation resistance at 500 V dc 100 Mohms per minute
- H.V. Breakdown test for 1 minute 2k V ac
- Screw termination
- Temperature range of 0 to +75 deg C
- Ideal for industrial and commercial applications
- Meets UL-498, NEMA WD 6:2002, CSA C22.2 No.42



ENGLISH

### Specifications:

Colour	White
Current Rating (Unwound)	13 A
Housing Type	Enclosed Satellite Reel
Number of Sockets	2+2
Reel Length	4 m
Socket Type	Type G - British, USB
Voltage Rating	230 V ac