



Security Tech Germany

## 80TI/45mm TITALIUM™ Padlocks

- High quality TITALIUM™ body with stainless steel appearance : Maximum corrosion resistance
- 6 Pin tumbler cylinder with anti-pick mushroom pins : Resists picking
- Through hardened steel alloy shackle : Resists saw attacks
- Rustfree internal components & chrome plated cylinder : Durable security
- Large tulip shaped keyhead : Convenient security
- Numerous KA suites available : Multiple site security
- Available blister packed or boxed : Informative generic packaging



Paracentric Keyway    Saw Resistant    Double Bolted    Keyed Alike Available



80TI/45 with 110/155 Hasp & Staple



"NanoProtect" Chrome Plating Helping to make rusty shackles a thing of the past

The flagship of the TITALIUM™ family of padlocks makes an impression with both its look and its technical properties. Within a massive lock body is a 6-pin precision cylinder with paracentric keyway giving protection against both forced or manipulative break-ins. A chrome plated cylinder core and hardened steel shackle with NANO Protect shackle coating assures security & high corrosion resistance.



80TI/45

ABUS UK Product Reference	ABUS Code	ABUS GPS	D mm	H mm	L mm	W mm	H mm	L mm	Weight gms	Key Blank	
										Reference	Code
80TI/45 Titalium Padlock	56230	7	24.5	29.5	8	45	82	21	200	80TI/40+45+50	57862
80TI/45 KA8011 Titalium Padlock	56231	7	24.5	29.5	8	45	82	21	200	80TI/40+45+50	57862