

ARCA 604021



Sample photo

Order symbol: ARCA 604021
Product nbr: 8120012
Description: Cabinet, PC
Remarks: Grey cover, 2-point locking, hinges on the long side

EAN: 6418074079237
EI. number:
 Finland: 3423100
 Denmark: 8212091100
 Sweden: 2500118
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		600	400	210	Ingress Protection (EN 60529): IP 66
inch:		23.6	15.7	8.3	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Gasket material:		PUR			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 6040		Mounting plate			
MPP ARCA 6040		Mounting plate perforated			
MPX ARCA 6040		Mounting plate			
DRS ARCA 604021		DIN rail frame set			
DRS ARCA 604030		DIN rail frame set			
IDS ARCA 6040		Inner door set			
PMK ARCA 40		Pole mounting kit			
Certificates:		Fimko			

ARCA 600x400x210

ARCA 400x600x210

