






ϕ .374 X .157
(9.5 X 4)




3 - M4 X 4.9 mm
TERMINAL SCREW AND
INTERNAL TOOTHED
LOCK WASHER

CHARACTERISTICS

ELECTRICAL RATING	15A 125VAC OR 250VAC UL APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	100 GMS
RELEASE FORCE MIN.	22 GMS
PRETRAVEL MAX.	.280 [7.1 mm]
OVERTRAVEL MIN.	.157 [4 mm]
MOVE. DIFF. MAX.	.040 [1.02 mm]
REST POSITION MAX.	1.437 (36.5 mm)
OPERATING POSITION	1.157 TO 1.575 [29.4 TO 40.0 mm]

DWN: JED
APVD: SB
DATE: 11-Aug-04

THIRD ANGLE PROJECTION



THE CONFIDENTIAL AND PROPRIETARY
INFORMATION CONTAINED IN THIS DOCUMENT
IS OWNED BY CHERRY ELECTRICAL PRODUCTS.
A DIVISION OF THE CHERRY CORPORATION WHO
MUST GIVE WRITTEN PERMISSION BEFORE THE
DOCUMENT OR INFORMATION CAN BE COPIED,
DISCLOSED OR USED IN ANY WAY.

TOLERANCE UNLESS SPECIFIED

	X.XX	X.XXX	ANGLES
	$\pm$ 0.02	$\pm$ 0.015	$\pm$ 5°

PROJECT / ESR

CHERRY
ELECTRICAL PRODUCTS
NAME / DESCRIPTION

11200 88TH AVENUE
PLEASANT PRAIRIE, WI 53158

SWITCH

B ITEM NO. GPTCRS01

SCALE: 2:1 SH 1 OF 1

C	12172	29-Oct-04	JED	SB
REV	ECN NO.	DATE	PREP	APVD