

Crimping pliers - CRIMPFOX-SC 1,5-M - 1212725

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for non-insulated slip-on sleeves 2.8 and 4.8 mm, 0.1 - 1.5 mm², B crimp

Why buy this product

- Crimping pliers for uninsulated slip-on sleeves
- Consistently high crimping quality
- Marked die stations for precise processing of corresponding cross sections
- Unlockable pressure lock



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 857840
Weight per Piece (excluding packing)	620.3 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	204 mm
Height	76 mm
Width (a)	22 mm

General

Compression	B crimp
Type of contact	Slip-on sleeve
Designation	Crimping position 1
Min. cross section	0.1 mm ²
Max. cross section	0.5 mm ²

Crimping pliers - CRIMPFOX-SC 1,5-M - 1212725

Technical data

General

AWG min	26
AWG max	22
Designation	Crimping position 2
Min. cross section	0.5 mm ²
Max. cross section	1 mm ²
AWG min	22
AWG max	18
Designation	Crimping position 3
Min. cross section	0.5 mm ²
Max. cross section	1.5 mm ²
AWG min	18
AWG max	16

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Accessories

Accessories

Mounting material

Crimping pliers - CRIMPFOX-SC 1,5-M - 1212725

Accessories

Replacement spring - CRIMPFOX/ SPR-1 - 1212069



Spare recuperating spring