



NO	DESCRIPTION	DATE
①	BACKGROUND FORMAT UPDATED	06.26.06'
②	BACKGROUND FORMAT UPDATED CENTER CONTACT → CHASSIS	06.04.09'
③	ADD CRIMP SIZE REQUIRED -40° C TO +85° C → -40° C TO +80° C	07.31.14'



STRIPPING DIMENSION
SCALE 2:1

1.0 MATERIALS

1.1 BODIES: BRASS PER JIS-C3604

2.0 FINISHES AND OTHERS

2.1 SEE BELOW TABLE FOR DETAILS.

3.0 MECHANICAL

3.1 FOR USE WITH 6U OR SIMILAR STYLE CABLE

3.2 CABLE ATTACHMENT: OUTER: CRIMP

3.3 CRIMP SIZE REQUIRED: FERRULE: 8.2(.324) HEX. CRIMP TOOL ③

4.0 ENVIRONMENTAL

4.1 OPERATING TEMPERATURE RANGE: -40° C TO +80° C ③

3	BODY	BRASS	1	NICKEL 100μ" MIN.
2	CHASSIS	BRASS	1	NICKEL 100μ" MIN.
1	NUT	BRASS	1	NICKEL 100μ" MIN.
NO	DESCRIPTION	MATERIAL	Q'TY	FINISH



APPROVED

by _____ DATE: _____

DESCRIPTION		F STRAIGHT PLUG CRIMP					
製圖	DRAWN	TOLERANCE		品名	18-07-1 NICKEL	6U	DATE
	Yoko	.X	±0.2	TITLE	\ROHS COMPLIANT	日期	03.06.93
檢圖	CHECK	.XX	±0.1	單位	mm(in)	版次	A-3
	Arc	.XXX	±0.05	比例	SCALE	DWG.NO.	18-0049
認定	APPROVAL	ANGLE	±5°	比例	4:1		
	Angela						