

Professionally approved products.

## Datasheet

# RS232-RS485 converter, without isolation

RS Stock number [523-7342](#)



### Features

- Point to point or multiple connection possible (Simultaneous monitoring or several devices)
- DCE/DTE adjustable
- Full duplex transfer over 4 lines
  - Only the data lines are converted
  - 25-pole socket on the RS232 side
  - Power supply via supplied mains adapter

### Applications

These Video Splitters can be used for:

- Monitor Testing and Burn-in
- Business Meetings
- Demonstrations
- Trade Shows
- Exhibits



## Professionally approved products.

### Specifications

RS232 Connection	D-Sub 25 Pin Female
RS485 Connection	Terminal Block (4 Clamps)
Power Supply	DC 9V, 200 mA
Data Transfer	up to ca. 100Kbit/s
Transfer Distance	Up to ca. 1km
Weight	60g
Number of Outputs	4
Signal Bandwidth	350 Mhz
Signal Type	VGA, SVGA, Multi-sync
Cable Length	65m
Dimensions (mm)	20x85x180
Enclosure	Metal