







NUMBER 178138



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST



NOTES

1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY

- ②. FINISH (CONTACT AREA): 0.38 μm MIN GOLD PLATING OVER Ni PLATING
③. FINISH (CONTACT AREA): 0.76 μm MIN GOLD PLATING OVER Ni PLATING
④. FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
~~⑤. FINISH (RETENTION LEG): TIN-LEAD PLATED (CONTACT TAIL) OVER NICKEL~~
⑥. FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

注記

1. 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂
コンタクト: 銅合金
リテンションレグ: 銅合金
②. めっき: コンタクト: 全面Ni下地
接触部: 0.38 μm MIN金めっき
③. めっき: コンタクト: 全面Ni下地
接触部: 0.76 μm MIN金めっき
④. めっき: コンタクト: 全面Ni下地
接触部: 2.0 μm MINスズめっき
~~⑤. めっき: リテンションレグとコンタクト半田付部~~
~~ニッケル下地の上に半田めっき~~
⑥. めっき: リテンションレグとコンタクト半田付部
ニッケル下地の上にスズめっき

⑥	④	2-178138-5	Y
⑥	③	2-178138-3	Y
⑥	②	2-178138-2	Y
⑥	④	1-178138-5	X
⑥	③	1-178138-3	X
⑥	②	1-178138-2	X
(FINISH)		製品番号 (PART NO.)	KEY

E1	REVISED PER ECO-11-005030	RK	HMR	23MAR11
LTR	REVISION RECORD	DR	CHK	DATE

WIRE RANGE		INSULATION DIA	NAME	
mm ² (AWG -)		mmφ	3 POS SINGLE ROW	
MATERIAL		FINISH	HORIZONTAL HDR ASS'Y FOR DYNAMIC D-3200	
SEE NOTE 注記参照		SEE NOTE 注記参照	一般公差 (GENERAL TOLERANCE)	
DR. 20/MAR/95 K.IKEDA		DE. 20/MAR/95 K.IKEDA		SIZE A3
CHK. 23/MAR/95 S.MANABE		APP. 23/MAR/95 S.MANABE		LOC J
				NUMBER C-178138
				SCALE 2-1
				REV. E1
				SHEET 1 OF 1