

Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

Adhesive	Repositionable Rubber
Application	Wire & Cable Marking
Approval/Compliance	UL Recognised
Article No.	131578
Brady Material No.	B-498
Material Type	Vinyl Cloth
Brand	CleanLift™ Series
Colour	Black on White
Environment	Freezer
Finish	Semi-gloss
Max. Service Temp. °C	80
Max. Wire/Cable Diameter (mm)	7.10
Order Reference	M-91-498
Printer Compatibility	BMP41; BMP51; BMP53
Shape	Rectangle
Size - Height (mm)	38.10
Size - Width (mm)	25.40
Additional Information	Repositionable
Total Qty per Pack	120 Label(s) / Box
Wire Gauge	10-4
Industry	Data & Telecommunications; Electrical
Min. Service Temp. °C	-40
QTY. per Row	1
Thickness (mm)	0.185