

Product Information

FTP125x50-Ø20 NL55

EAN 4031582332056

Wheel centre made of cast iron, Tread:
Polyurethane, casted, precision ball bearing

| | |
|-------------------|----------------|
| Wheel diameter | 125 mm |
| Width of Tread | 50 mm |
| Axle Hole Ø | 25 mm |
| Hub length | 55 mm |
| Temperature | - 20 / + 60 °C |
| Standard | EN 12533 |
| Hardness of tread | A 92 Shore |

