



## Main

Range of product	PratiKa
Product or component type	Wander socket
Device short name	PratiKa fast
Plug, socket category	Low voltage
Industrial socket type	Fast
Poles description	3P + E
Network type	AC
Outlet standard	Industrial

## Complementary

Plug, socket, control station shape	Straight
[In] rated current	32 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Self-extinguishing engineering polymer housing:
Contacts material	Brass sleeves:
Connections - terminals	Fast connection
Cable cross section	2.5...6 mm <sup>2</sup>
Cable outer diameter	11.5...21 mm
Cable entry	Cable gland
Thread type	Pg 21
Product weight	0.308 kg
Height	99 mm
Width	99 mm
Depth	164 mm
Colour	Grey ( RAL 7035 )
Voltage colour	Red

## Environment

Standards	IEC 60309-1 IEC 60309-2
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-1
Relative humidity	90 % ( 20 °C ) 70 % ( 30 °C ) 50 % ( 40 °C )
Ambient air temperature for operation	35 °C ( 86400 s ) -25...40 °C