


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

MOD	LOC	DIST	P	F	REVISIONS				
4	BD	35			ZONE	LTR	DESCRIPTION	DATE	APPD
						C	REDRAW W/O CHANGE PER EC 0020-600-94	07/29/94	AF



1. CABLE RANGE 5.08 [.200] - 6.35 [.250] WHEN USED WITH GRIPPER P/N 207387-1.
2. CABLE RANGE 6.35 [.250] - 8.89 [.350] WHEN USED WITH GRIPPER P/N 207387-2 OR 207387-4.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± -			DR 07/29/94 M.BINNER	AMP AMP Incorporated Harrisburg, PA 17105-3608	
MATERIAL THERMOPLASTIC COLOR: BLACK			CHK 8-8-94 R.STONE		
FINISH -			APPD 8-9-94 A.FRANTUM	NAME CABLE BOOT, FLEXIBLE, SIZE 17, CPC	
			APPD 8-9-94 A.FRANTUM	SIZE B	CAGE CODE 00779
			PRODUCT SPEC -	DRAWING NO C-207241	
			APPLICATION SPEC -	SCALE 2:1	SHEET 1 OF 1
			WEIGHT -		