

# Insulated IP65 ABS Plastic Enclosures

- ✓ IP65 Rated
- ✓ Strong ABS Enclosure
- ✓ Back Plate Included
- ✓ Fixing Brackets Included



Part Number	Description
PBE2821013	Height: 280 x Width: 210 x Depth: 130mm
PBE332513	Height: 330 x Width: 250 x Depth: 130mm
PBE4030016	Height: 400 x Width: 300 x Depth: 165mm
PBE403019	Height: 400 x Width: 300 x Depth: 195mm
PBE503519	Height: 500 x Width: 350 x Depth: 195mm
PBE504017	Height: 500 x Width: 400 x Depth: 175mm
PBE604020	Height: 600 x Width: 400 x Depth: 200mm
PBE605022	Height: 600 x Width: 500 x Depth: 220mm
PBE705024	Height: 700 x Width: 500 x Depth: 245mm
PBE806026	Height: 800 x Width: 600 x Depth: 260mm

**⚠ Important Safety Notice ⚠**

It is the responsibility of the person installing the electrical equipment to ensure that the installation meets the requirements of the IET wiring regulations and is therefore 'fit for purpose'. Factors such as correct selection of components, cable sizing, protective devices and Earth bonding are all critical and should be checked prior to full testing and power-up. Any other regulations applicable to the equipment being installed such as the Machinery Directive and current health and safety legislation must also be adhered to. Terminals should be checked periodically to ensure correct tightness.




✓ Strong ABS Enclosure / ✓ Back Plate and Fixing Brackets Included

**Dimensions Table**

Dimensions provided are for guidance purposes only

Part number	External Dimensions			Internal Depth	Mounting plate		Other Information (GPTB = Gland Plate Top & Bottom)
	H (mm)	W (mm)	D (mm)	ID	H3 (mm)	W3 (mm)	
746-7393	280	210	130	106	230	150	1 ⚠ Lock, No Glandplate
769-6125	330	250	130	108	280	190	1 ⚠ Lock, No Glandplate
746-7396	400	300	165	139	350	240	2 ⚠ Locks, No Glandplate
746-7390	400	300	195	165	350	240	2 ⚠ Locks, No Glandplate
769-6128	500	350	195	168	450	288	2 ⚠ Locks, No Glandplate
746-7400	500	400	175	145	450	340	2 ⚠ Locks, No Glandplate
746-7403	600	400	200	170	545	340	2 ⚠ Locks, No Glandplate
769-6122	600	500	220	185	530	445	2 ⚠ Locks, No Glandplate
746-7407	700	500	245	205	630	450	2 ⚠ Locks, No Glandplate
769-6131	800	600	260	225	725	540	3 ⚠ Locks, No Glandplate

\* key:  = back plate

