



OUR OFFER

Schneider Electric – Altivar 312

Altivar 312 Inverter Drives

- For compact machines from 0.18 to 15 kW
- Modbus and CANopen integrated as standard
- Integrated operator panel and EMC filter
- Rapid programming in just a few clicks
- A wide choice of voltage ranges

1-Phase Input

Stock-No.	MPN	Input Voltage	Power Rate
701-0697	ATV312H018M2	200-240 V	0.18 kW
701-2707	ATV312H037M2	200-240 V	0.37 kW
701-2700	ATV312H055M2	200-240 V	0.55 kW
701-2704	ATV312H075M2	200-240 V	0.75 kW
701-2713	ATV312HU11M2	200-240 V	1.1 kW
701-2716	ATV312HU15M2	200-240 V	1.5 kW
701-2710	ATV312HU22M2	200-240 V	2.2 kW



3-Phase Input

Stock-No.	MPN	Input Voltage	Power Rate
820-0885	ATV312H018M3	200-240 V	0.18 kW
820-0889	ATV312H037M3	200-240 V	0.37 kW
701-2729	ATV312H037N4	380-500 V	0.37 kW
820-0898	ATV312H055M3	200-240 V	0.55 kW
701-2722	ATV312H055N4	380-500 V	0.55 kW
820-0891	ATV312H075M3	200-240 V	0.75 kW
701-2726	ATV312H075N4	380-500 V	0.75 kW
822-6213	ATV312H075S6	525-600 V	0.75 kW
820-0895	ATV312HU11M3	200-240 V	1.1 kW
701-2735	ATV312HU11N4	380-500 V	1.1 kW
820-0905	ATV312HU15M3	200-240 V	1.5 kW
701-2738	ATV312HU15N4	380-500 V	1.5 kW
822-6219	ATV312HU15S6	525-600 V	1.5 kW
820-0908	ATV312HU22M3	200-240 V	2.2 kW
701-2732	ATV312HU22N4	380-500 V	2.2 kW
822-6184	ATV312HU22S6	525-600 V	2.2 kW
820-0902	ATV312HU30M3	200-240 V	3 kW
701-2741	ATV312HU30N4	380-500 V	3 kW
820-0911	ATV312HU40M3	200-240 V	4 kW
701-2744	ATV312HU40N4	380-500 V	4 kW
822-6178	ATV312HU40S6	525-600 V	4 kW
820-0914	ATV312HU55M3	200-240 V	5.5 kW
701-2748	ATV312HU55N4	380-500 V	5.5 kW
822-6134	ATV312HU55S6	525-600 V	5.5 kW
820-0918	ATV312HU75M3	200-240 V	7.5 kW
701-2757	ATV312HU75N4	380-500 V	7.5 kW
823-0319	ATV312HU75S6	525-600 V	7.5 kW
820-0927	ATV312HD11M3	200-240 V	11 kW
701-2750	ATV312HD11N4	380-500 V	11 kW
822-6011	ATV312HD11S6	525-600 V	11 kW
820-0920	ATV312HD15M3	200-240 V	15 kW
701-2754	ATV312HD15N4	380-500 V	15 kW
822-6017	ATV312HD15S6	525-600 V	15 kW



For more technical information please visit:

www.rs-online.com