

805-0972

## 156-00155

C Clip Tie, 50lbs, Clip Dia. .26"-.32" Max Bun Dia. 1.38" PA66HS Tie, HIRHS Mount, BLK 500/pk

Article Number: 156-00155

Part Number: 156-00155

Type: T50SVC65



### Base Data

---

**Part No.** 156-00155

**Type** T50SVC65

**Color** Black

**Features** C Clips secure cables to tubular frame rails. The cable tie is fastened to the tubular frame rail and the solar cable snaps into the clip. The cable can be removed from the clip and reinstalled without additional fasteners.

**Identification Plate** none

**Position**

### Product Dimensions

---

**Min. Tensile Strength** 50 lbs / 225 N

**Length (L)** 6.10 " / 155 mm

**Attach to Diameter** 0.26" - 0.32"

**Width (W)** 0.19 " / 4.7 mm

**Max. Ø Bundle** 1.38 " / 35.0 mm

**Attach to Ø**

6.5 - 8.0 mm

**Material and Specifications**

---

**Material**

Polyamide 6.6 heat stabilized (PA66HS) / Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

**Flammability**

UL94 V2

**Material Specification**

RoHS

**Operating  
Temperature**

-40 °C to +105 °C