

Product data sheet

Characteristics

XZCP1041L10

pre-wired connectors XZ - elbowed female - M8
- 4 pins - cable PUR 10m

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

| | |
|------------------------------------|-------------------------------------|
| Commercial Status | Commercialised |
| Accessory / separate part category | Cabling accessories |
| Accessory / separate part type | Pre-wired connectors |
| Series name | General purpose |
| Electrical connection | Elbowed female connector M8, 4 pins |
| Collar material | Metal |
| Status LED | Without |
| Cable length | 32.81 ft (10 m) |

Complementary

| | |
|--------------------------------|--------------------------|
| Cable connector fixing | Screw-on |
| Cable outer diameter | 0.2 in (5.2 mm) |
| Cable composition | 4 x 0.34 mm ² |
| Wire insulation material | PUR |
| [Ue] rated operational voltage | 75 V DC 60 V AC |
| [In] rated current | 4 A |
| Contact resistance | <= 5000 µOhm |
| Insulating resistance | >= 1 GΩ |
| Product weight | 0.79 lb(US) (0.36 kg) |

Environment

| | |
|---------------------------------------|---|
| IP degree of protection | IP67 |
| Ambient air temperature for operation | 23...176 °F (-5...80 °C) (flexing) -40...176 °F (-40...80 °C) (static) |
| Ambient air temperature for storage | -40...176 °F (-40...80 °C) |

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 22483 - MACHINE CABLES |
| Discount Schedule | DS3 |
| GTIN | 00785901861317 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.70 |
| Product availability | Non-Stock - Not normally stocked in distribution facility |
| Returnability | Y |
| Country of origin | DE |

Offer Sustainability

| | |
|--------------------------|---|
| Sustainable offer status | Not Green Premium product |
| RoHS | Compliant - since 0649 - Schneider Electric declaration of conformity |

Contractual warranty

| | |
|--------|-----------|
| Period | 18 months |
|--------|-----------|