

Datasheet

Stock No: 811-4396

RS Pro 4 Core Unscreened White 3184Y Power Cable



Conductors	32/0.20mm Plain Annealed Copper (Class 5 to IEC 60228)
Insulation	PVC (Type T11 to BS 7655)
Insulation Radial Thickness	0.60mm
Diameter over Insulation	2.52mm (Nominal)
Number of Cores	4
Core Colours	Brown, Black, Grey & Green/Yellow
Sheath	PVC (Type TM2 to BS 7655)
Sheath radial thickness	0.90mm
Overall Dimensions	7.90mm (Nominal)
Voltage Rating	300/500V
Conductor Resistance	19.5Ω/km at 20°C (Nominal)
Cable Weight	104.5 kg/km (Nominal)
Standards	BS EN 50525-2-11 Table 4.2
Harmonization Code	H05VV-F
Sheath Colour	White
Reel Length	100m