


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			D	REDRAWN, REV. PER G-1476, G-1175, P85-0063 & P85-0064	12/1/86
			E	OBSOLETE 2--3 PER G-2393	3/23/87
			F	OBSOLETE 2--2 PER G-3358	4-22-88
			G	REV PER G-4732	JT 7/2/88
			H	REV / G-019392	LO 9/92
			J	REV / 0720-0242-93	TQ 3-9-93
			K	REV / 0610-0094-98	2-3-99
			L	ADDED - 1 8-24 PER 063A-0314-00	8/may/00
			M	REV PER 063A-0274-01	24/may/01



- 1 WIRE INSULATION DIA. = .105-.140
- 2 TONGUE MATERIAL THK. = .031±.002
- 3 22-18 MARKING FOR MILITARY, COMMERCIAL RANGE 22-16
- 4 TIN PLATE (ASTM B 545) .000100 MIN THK.
- 5 PRELIMINARY - NOT FOR PRODUCTION
- 6 SUPERSEDED BY 8-34541-1

OBSOLETE	RED	50	LOOSE PIECE, BAG	8-34541-5
	RED	100	LOOSE PIECE, BOX	8-34541-1
OBSOLETE	BLACK	5,000	34541-1 ON TAPE, REEL	2-34541-4
	RED	100	ON TAPE, SM. BOX	2-34541-3
OBSOLETE	RED	1,000	ON TAPE, LG. BOX	2-34541-2
	RED	5,000	34541 ON TAPE, REEL	2-34541-1
OBSOLETE	BLACK	-#	LOOSE PIECE	34541-1
	RED	-#	LOOSE PIECE	34541

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.008 ANGLES ±		CONTRACT NO DR UTA/RFB 9-24-85		AMP INCORPORATED Harrisburg, Pa.	
MATERIAL INSULATION: NYLON - RED BODY & SLEEVE: COPPER PER (ASTM B 152)		CHK APPD DSGN APPD OTHER APPD		NAME TERMINAL, PIDG™, SPADE WIRE SIZE: 22-16	
FINISH BODY: 4		SIZE B		FSCM. NO 00779	DRAWING NO 34541
		SCALE NTS		SHEET 1 OF 1	