

SMALL RS LIGHT BOX 462-8371

Dimensions -W. 333 D. 333 H. 73mm

Non-slip rubber feet

Supply voltage - 230V AC 50 Hz

Fluorescent tubes - 2 x 300mm 8W Daylight (cool white)

Viewing area - 300 x 300mm

Correlated colour temperature 4300°K

LARGE RS LIGHT BOX 462-8343

Dimensions -W. 643 D. 491 H. 123mm

Non-slip rubber feet

Supply voltage - 230V AC 50 Hz

Fluorescent tubes - 2 x 600mm 20W Daylight (cool white)

Viewing area - 610x 458mm

Correlated colour temperature 4300°K

The base on the large unit incorporates a stand that allows the unit to be elevated in landscape to the following four angles; 35°; 45°; 55° and 65°.

Both large and small units are constructed in 18swg (1.2mm) mild steel and powder coated in white. Both feature a 5mm thick opal acrylic light screen.