

Housing - HC-D 50-TMQ-76/M1PG29S - 1775839


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, with double locking latch, height 76 mm, with screw connection, 1x Pg29, lateral cable entry



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 038380
Weight per Piece (excluding packing)	414.0 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	76 mm
Width	56 mm
Length	82 mm
Wrench size, union nut	37 mm
External cable diameter	18 mm ... 27 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D25, A16/A32
Type	D50
Housing type	Sleeve housing
Locking type	With double locking latch
No. of cable outlets	1
Cable exit	Lateral

Housing - HC-D 50-TMQ-76/M1PG29S - 1775839

Technical data

General

Screw connection	with
Type of the screw connection	1x Pg29
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Cable gland material	Nickel-plated brass
Cable seal material	NBR
Material lock	Steel, galvanized

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC

Ex Approvals

Housing - HC-D 50-TMQ-76/M1PG29S - 1775839

Approvals

Approvals submitted

Approval details

EAC

Drawings

Dimensioned drawing

