

Compact, powerful, rechargeable and intelligent multi-beam headlamp with REACTIVE LIGHTING technology that automatically adjusts brightness and beam pattern. **215 lumens**



The TIKKA RXP multi-beam headlamp offers **215 lumens brightness**.

Compact and USB rechargeable, it is ideal for dynamic, energetic activities. With its REACTIVE LIGHTING technology, lighting becomes powerful and intelligent: a sensor analyses the ambient light and adjusts the beam pattern and brightness instantly and automatically to user requirements, thus optimizing burn time and reducing the need for manual operation.

Description

- Greater burn time, visual comfort and minimal handling thanks to REACTIVE LIGHTING technology:
 - the light sensor automatically adjusts brightness and optimizes burn time
 - depending on the chosen burn time (3h30, 6 h, 12 h), brightness automatically self-regulates in three modes : MAX POWER, STANDARD, MAX AUTONOMY,
 - Reduced manual operation
- Two beam patterns (wide and focused) and several lighting modes meet the need for high-performance lighting in dynamic outdoor activities: proximity or distance vision and rapid movement
- Maximum brightness: 215 lumens
- Lamp can be used with CONSTANT LIGHTING technology, to ensure constant lighting over time.
- Lock function to avoid accidentally turning it on during transit or storage
- Red lighting mode preserves night vision (red LED and strobe mode)
- Rechargeable 1800 mAh Lithium-Ion battery:
 - universal charging with micro USB port
 - battery charge indicator
 - performs well at low temperatures
 - can be replaced with standard battery pack (not included) for use in remote areas
- Washable headband, designed for dynamic activities (secure and absorbent)
- Profiles and customized burn times with OS by Petzl software, free for download at www.petzl.com/OS

Specifications

- Weight: 115 g
- Technology: REACTIVE LIGHTING or CONSTANT LIGHTING
- Beam pattern: wide, mixed, focused
- Energy: 1800 mAh Lithium-Ion rechargeable battery (included)
- Recharge time: 4,5 h
- Battery compatibility: alkaline, lithium and Ni-MH, with the standard battery pack (not included)
- Watertightness: IP X4 (water resistant)
- Certification(s): CE
- Colour black/white