

Re-usable Nitrile 37-355

Technical Specifications

proFood™

Product description

Unsupported cotton flocked nitrile protective gloves.

Cuff finish : straight

Glove material

- copolymer of Butadiene-Acrylonitrile
- cotton flock

The glove is treated with Actifresh® - Sanitized®.

Characteristics

- Excellent physical properties
- Very good dexterity
- Silicon-free
- Use against following chemicals : Oils and greases ; Solvents ; Alcohols ; Aliphatic hydrocarbons ; Acids and Bases
- Tensile at break : 25 - 35 Mpa
- Elongation : 450 - 550 %
- Modulus 300 % : 8 - 12 Mpa
- Individually packed in pairs

Performance specifications

Abrasion resistance : Performance level 4
(> 8000 cycles)

Blade cut resistance : Performance level 1
(index 1.4)

Tear resistance : Performance level 0 (< 10 N)

Puncture resistance : Performance level 2
(average 77 N)

Liquidproof - Acceptable Quality level 0.65 or EN performance level 3

Chemical permeation : upon request

Gloves conform to the requirements of the European Directive 89/686/EEC and to the European standards EN 420, EN 388 and EN 374. They are categorised in "Complex Design" (= Protection against Mortal risks).

EC-type examination certificate received from:

ITF LYON

Avenue Guy de Collongue

B.P. 60

F-69132 ECULLY CEDEX

EC-Quality of production by means of monitoring :

BRITISH STANDARDS INSTITUTION

PO Box 375

GB - MK14 6LL Milton Keynes

Gloves conform to the requirements of the European Directive 89/109/EEC "Materials and Articles to Come into Contact with Foodstuffs", EC-type examination certificate received from:

Laboratoire National d'Essais

5, Avenue Enrico Fermi

F-78197 Trappes Cedex

Migration against ethanol 10% : < 10 mg/dm²

Migration against acetic acid 3% : < 10 mg/dm²

Migration against iso-octane : < 10 mg/dm²

Application

Suitable for contact with any food.

Limitations of use

Do not use against flames or temperatures < -25 °C or > 100 °C.

Poor versus aromatic hydrocarbons, chlorinated solvents and many ketones.

Type	Finish	Reference	(EN) Sizes	Colour	Thickness	Length
Flocked	Honeycomb	37-355	7, 8, 9, 10	Blue	0.38 mm	330 mm

For more details (i.e. chemical protection), please contact :
Ansell Protective Products, Wijngaardveld 34 C, B-9300 Aalst
Tel. : +32 - 53 71 05 05 Fax : +32 - 53 71 13 42