



Marquardt Mechatronik GmbH  
Schloss-Str. 16  
78604 Rietheim-Weilheim  
Germany


Phone: +49 (0) 7424 / 99-0  
Fax: +49 (0) 7424 / 99-2399  
Net: www.marquardt.de  
E-mail: marquardt@marquardt.de

## Product image / Drawings



Similar to original product

## Technical data

<b>Product number</b>	<b>4021.4620</b>
Actuator color / printing	
Product family	Slide switches
Actuation type	direct
Weight	5.649 g
ROHS conform	yes
Switching function	Changeover switch (DPDT)
Material fixed contact	Cu silver-plated
Number of poles	2 - pole
connections	PCB terminal
Mechanical life endurance	1E4
Rating IEC	10 A 250 V AC 1E4
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm
Insulation resistance (new condition)	> 100 (500 V DC) MOhm
Voltage strength at 250 V	function insulation / basic insulation 1 500 V reinforced insulation 3 000 V small contact distance 500 V
Proof tracking	250 PTI
Insulation spacing	acc. to EN 61058 for reinforced or double insulation
Protection type	Connection IP 40 Actuator IP 40
Ambient temperature	-20 °C ... +80 °C
Ambient temperature	-20 °C ... +55 °C
Storage temperature	-40 °C ... +80 °C
Flammability	UL 94 V-2
Glow wire test temperature	850 °C
Actuators and additional actuators	slide: PA, red, with actuator slot, identification black
Housing description	housing: PA, black, housing without fastening lugs base plate: PA glass fiber-reinforced, natural
Connection surface	bearing connection silver plated external connection silver plated
Contact material	CuSn silver plated
Contact distance	≥ 3 mm
Contact type	slide contact

Plug force of the terminals	≤ 60 N
Approval marks	ENEC 15 / cULus
Miscellaneous	slide with actuating slot / 5 A or 10 A only as voltage selector switch
Additional labeling	site, year, week of manuf. acc. to DIN EN 60062
Type of fastening	screw fastening
Degree of pollution	3
Stock version	●