

Datasheet

RS 4 Core Screened Industrial Cable, PVC Sheath, 3.2mm OD, 0.055 mm² CSA 0.25 A, 300 V, 25m

Stock Number - 660-0381



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):300

Flammability Test: IEC60332-1



ENGLISH

Construction:

Conductor:Tinned Copper

Conductor Dia. (mm): 0.10±0.008 x 7

Insulation: PVC

Insulation Dia. (mm): 0.7±0.05 x 4C

Tape: Mylar Spiral

Coverage:≥115%

Braid Shield : Tinned Copper

Conductor Dia. (mm): 0.10

Conductor Qty: 16x5

Pitch(mm):

Coverage : 91%

ID Thread : Green, White/Green

A rip cord : 210 D

Jacket: FR-PVC

Outer Dia. (mm): 3.2±0.1

Colour:

The colour of the insulation: Red , Blue , Green ,
Yellow

The jacket colour: Black

Marking(3times/m):

RS 6600381 7 - 1 - 4C

Electrical Characteristics:**Max.Conductor DC Resistance at 20°C (Ω /Km) :**

<345

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :

>200

Current Rating : 0.25 A