

Specifications for BMP41/BMP51/BMP53 Labelmaker Tape

Adhesive	Permanent Acrylic
Application	Bin & Storage Identification; General & Industrial Identification; Indoor & Outdoor Grade Facility & Safety Identification
Article No.	143399
Brady Material No.	B-595
Material Type	Vinyl
Colour	White on Red
Finish	Gloss
Laboratory Application	Well Plates;General Identification
Description	Durable, low-shrink vinyl with our most aggressive adhesive. Conforms to irregular, curved, rough and highly textured surfaces (painted cinder blocks, uneven wood, textured plastics, paper jacketed pipes, powder coated surfaces). Also adheres to difficult low energy surface items (PVC piping, blow-moulded equipment cases, ABS plastics, recycled plastics)
Max. Service Temp. °C	82
Order Reference	MC-500-595-RD-WT
Printer Compatibility	BMP41; BMP51; BMP53
Shape	Continuous
Size - Length (m)	7.62
Size - Width (mm)	12.70
Total Qty per Pack	1 Label(s) / Box
Voice/Data Application	Backbone Labelling
Industry	Facility & Safety Industry; Process
Layout	Continuous Roll
Min. Application Temp. °C	-18
Min. Service Temp. °C	-40
Thickness (mm)	0.1