

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




16-channel digital output module with spring-cage connection and redundant voltage supply. Suitable for Yokogawa card SDV 541.

The figure shows a version with a screw connection



Key commercial data

Packing unit	1
GTIN	 4 046356 697972
Custom tariff number	85369010

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	162 mm
Height	112 mm
Depth	80 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
---------------------------------	------------------

General

Note	Voltage monitoring on the module does not work in combination with upstream HESILED fuse terminal blocks with integrated LED display.
Max. permissible operating voltage	24 V DC ±5 %
Max. perm. current (per branch)	100 mA
Max. permissible current (separate power supply)	6.3 AT (F150, F151) plug-in fuse (5x20, 6.3 A), DIN 41662
Status display	Green LED (supply), yellow LED (channel)
Mounting position	any
Standards/regulations	DIN EN 50178

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Technical data

General

Rated surge voltage	basic insulation
Pollution degree	2
Surge voltage category	III

Connection data for connection 1

Connection name	Field level
Connection method	Spring-cage connection
Number of positions	32
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14

Connection data for connection 2

Connection name	Controller level
Number of connections	2
Connection method	Yokogawa KS-compatible
Number of positions	50

Supported controller

Controller	YOKOGAWA ProSafe-RS
- suitable I/O card	SDV541

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27069203
eCl@ss 7.0	27069203

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001437
ETIM 5.0	EC001437

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Classifications

UNSPSC

UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Accessories

Accessories

System cable

Cable - FLK 50-PA/EZ-DR/KS/ 100/YUC - 2900991



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 1.0 m.

Cable - FLK 50-PA/EZ-DR/KS/ 200/YUC - 2314299



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 2.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 300/YUC - 2314309



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 3.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 400/YUC - 2314312



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 4.0 m

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Accessories

Cable - FLK 50-PA/EZ-DR/KS/ 500/YUC - 2321499



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 5.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 600/YUC - 2314927



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 6.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 700/YUC - 2321509



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 7.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 800/YUC - 2314930



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 8.0 m

Cable - FLK 50-PA/EZ-DR/KS/ 900/YUC - 2321512



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 9.0 m

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Accessories

Cable - FLK 50-PA/EZ-DR/KS/1000/YUC - 2314325



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 10.0 m

Cable - FLK 50-PA/EZ-DR/KS/1100/YUC - 2321389



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 11.0 m

Cable - FLK 50-PA/EZ-DR/KS/1200/YUC - 2321525



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 12.0 m

Cable - FLK 50-PA/EZ-DR/KS/1300/YUC - 2321392



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 13.0 m

Cable - FLK 50-PA/EZ-DR/KS/1400/YUC - 2321402



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 14.0 m

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Accessories

Cable - FLK 50-PA/EZ-DR/KS/1500/YUC - 2314338



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 15.0 m

Cable - FLK 50-PA/EZ-DR/KS/1600/YUC - 2321538



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 16.0 m

Cable - FLK 50-PA/EZ-DR/KS/1700/YUC - 2321541



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 17.0 m

Cable - FLK 50-PA/EZ-DR/KS/1800/YUC - 2321554



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 18.0 m

Cable - FLK 50-PA/EZ-DR/KS/1900/YUC - 2321567



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 19.0 m

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Accessories

Cable - FLK 50-PA/EZ-DR/KS/2000/YUC - 2314503



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 20.0 m

Cable - FLK 50-PA/EZ-DR/KS/2500/YUC - 2314516



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 25.0 m

Cable - FLK 50-PA/EZ-DR/KS/3000/YUC - 2314529



Round cable set, with two 50-pos. molded socket strips (1:1 connection). Length of cable: 30.0 m

Cable - FLK 50-PA/EZ-DR/KS/5000/YUC - 2318981



Assembled round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 50.0 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 100/YUC - 2904739



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 1 m

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/ 200/YUC - 2904740



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 2 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 300/YUC - 2904741



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 3 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 400/YUC - 2904742



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 4 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 500/YUC - 2904636



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 5 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 600/YUC - 2904743



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 60 m

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/ 700/YUC - 2904744



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 7 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 800/YUC - 2904745



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 8 m

Cable - FLK 50-PA/EZ-DR/HF/KS/ 900/YUC - 2904746



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 9 m

Cable - FLK 50-PA/EZ-DR/HF/KS/1000/YUC - 2904637



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 10 m

Cable - FLK 50-PA/EZ-DR/HF/KS/1500/YUC - 2904638



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 15 m

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/2000/YUC - 2904487



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 20 m

Cable - FLK 50-PA/EZ-DR/HF/KS/2500/YUC - 2904639



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 25 m

Cable - FLK 50-PA/EZ-DR/HF/KS/3000/YUC - 2904640



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 30 m

Cable - FLK 50-PA/EZ-DR/HF/KS/3500/YUC - 2904641



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 35 m

Cable - FLK 50-PA/EZ-DR/HF/KS/4000/YUC - 2904642



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 40 m

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Accessories

Cable - FLK 50-PA/EZ-DR/HF/KS/4500/YUC - 2904643



Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 45 m

Cable - FLK 50-PA/EZ-DR/HF/KS/5000/YUC - 2904644




Assembled halogen-free round cable with two molded 50-pos. socket strips (1:1 connection). Cable length: 50 m

Drawings

Output module - UM-2KS50/16DO/RS/ZFKDS - 2902931

Dimensioned drawing

Bestückte Leiterplatte / assembled pcb



Anwendungsdiagramm / application diagram

