



4. OUTER JACKET: PVC 45Pa BLACK(1101) (RoHS)
3. HDMI C/M U type, terminal gold flashed 15u", plug gold flashed, w/40#cabletrough for automatical soldering RoHS
2. HDMI A/M U type, terminal gold flashed 15u", plug gold flashed, w/40#cabletrough for automatical soldering RoHS
1. (40#1P+D+A+MY)4C+(36#1P+1)+40#3C+32#1C+A+S BLACK(1101) OD:2.7MM 1200MM RoHS

A	FIRST EDITION	ECB	14/11/11
REV.	ECR	DESCRIPTION	C.N. DATE
		Rotronic Co., Ltd.	
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCE TELEPHONE: 317</small>		ROLINE Slim HDMI High Sp. Cable w/Ethernet, A-C, 1.2m	
<small>DIMENSIONS</small> 0.00 TO 30.00mm ±0.10mm 30.01 TO 80.00mm ±0.13mm 80.01 TO 150.00mm ±0.15mm 150.01mm ±0.20mm		<small>TOLERANCES</small> ±0.10mm ±0.13mm ±0.15mm ±0.20mm	
<small>WATERAL</small> FINISH		<small>PART NO.</small> 2162-3574	
<small>SCALE</small> SHEET 1/1 UNIT MM SIZE A4 PDA A		<small>REV.</small> A	