

















Side clip on housing

Style	Ordering number	Cable entry			Description	Outline drawing dimensions in mm
Surface-mounted housing bottom entry						
		PG	PG	PG		
	41.50.16.00				HA.16.AG-LB	
	51.41.50.16.00				HA-K.16.AG-LB	
With cover						
	41.52.16.00				HA.16.AGD-LB	
	51.41.52.16.00				HA-K.16.AGD-LB	
Surface-mounted housing side entry standard construction						
	41.60.16.05	16			HA.16.SG-LB.1.16	
	41.60.16.79				HA.16.SG-LB.1.16.Z	
	41.60.16.06	2x16			HA.16.SG-LB.2.16	
	41.60.16.95				HA.16.SG-LB.2.16.Z	
	51.41.60.16.05	16			HA-K.16.SG-LB.1.16	
	51.41.60.16.79				HA-K.16.SG-LB.1.16.Z	
	51.41.60.16.06	2x16			HA-K.16.SG-LB.2.16	
	51.41.60.16.95				HA-K.16.SG-LB.2.16.Z	
high construction						
	49.60.25.05	16			HD.25.SG-LB.1.16	
	49.60.25.79				HD.25.SG-LB.1.16.Z	
	49.60.25.06	2x16			HD.25.SG-LB.2.16	
	49.60.25.95				HD.25.SG-LB.2.16.Z	
	49.60.25.07	21			HD.25.SG-LB.1.21	
	49.60.25.80				HD.25.SG-LB.1.21.Z	
	49.60.25.08	2x21			HD.25.SG-LB.2.21	
	49.60.25.96				HD.25.SG-LB.2.21.Z	
	51.49.60.25.05	16			HD-K.25.SG-LB.1.16	
	51.49.60.25.79				HD-K.25.SG-LB.1.16.Z	
	51.49.60.25.06	2x16			HD-K.25.SG-LB.2.16	
	51.49.60.25.95				HD-K.25.SG-LB.2.16.Z	
	51.49.60.25.07	21			HD-K.25.SG-LB.1.21	
	51.49.60.25.80				HD-K.25.SG-LB.1.21.Z	
	51.49.60.25.08	2x21			HD-K.25.SG-LB.2.21	
	51.49.60.25.96				HD-K.25.SG-LB.2.21.Z	