



### KEY FEATURES

- 1U rack-mount
- Atom D2550 CPU
- 2GB DDR3 RAM
- 320GB HDD
- Windows 7 Pro 32bit

### SPECIFICATION

CPU	Intel Atom D2550, 1.86GHz dual core, 1MB cache
Chipset	Intel NM10
Memory	2GB DDR3, Upgradeable to 4GB
Storage	320GB 2.5" SATA hard drive, 1x mSATA (shared with Mini PCIe)
I/O ports	<ul style="list-style-type: none"> <li>• 1 x VGA</li> <li>• 1 x HDMI</li> <li>• 2 x Gigabit LAN</li> <li>• 2 x Audio</li> <li>• 2 x RS232</li> <li>• 2 x USB 3.0</li> <li>• 4 x USB 2.0</li> </ul>
Expansion slots	Mini PCIe slot (shared with mSATA)
Power input	AC input (full range)
Operating system	Windows 7 Pro 32bit
Dimensions	430 x 230 x 44.5mm
Operating temperature	0 to 45°C
Cooling	Quiet chassis fans, PSU fan

STE-1U-D2550-SYS\_v2014\_01\_Rev2.pdf

Technical Specifications quoted are qualified and verified but do not indicate the maximum performance limitations of the equipment. Specifications are subject to change without notice. E & OE Issue A