

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130028-0042](#)
Status: **Active**
Overview: [DeviceNet* Solutions](#)
Description: Micro-Change® (M12) Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 22 AWG, DeviceNet* Thin Stranded Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Cordsets
 Series [130028](#)
 Connector End A Micro-Change® (M12)
 Connector End B Micro-Change® (M12)
 IP Rating IP67
 Overview [DeviceNet* Solutions](#)
 Product Name DeviceNet*, Micro-Change® (M12)
 Protocol DeviceNet*
 Region Europe
 Type Double Ended
 UPC 78678801127

Physical

Cable Diameter 12.10mm (.480")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Gray
 Coupling Style Threaded
 Gender Male-Female
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body PVC
 Material - Contact Copper Alloy
 Material - Coupling Nut Die-Cast Zinc
 Material - Plating Mating Gold over Nickel
 Net Weight 15.710/g
 Orientation Straight
 Poles 5
 Temperature Range - Operating -20°C to +80°C
 Wire Size AWG 22
 Wire/Cable Type Shielded-Twisted Pair

Electrical

Current - Maximum per Contact 4A
 Voltage - Maximum 250V AC/DC

Material Info

Old Part Number DND22A-M050

Reference - Drawing Numbers

Sales Drawing SD-130028-001




image - Reference only

EU RoHS

RoHS Compliant by Exemption


REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130028Series

This document was generated on 10/23/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION