







注)
NOTE.

1. 各部のそりは0.5最大
WARPING:0.5MAX.
2. サークットNO.はNO. " 1 " のみ表示
CIRCUIT NO.: "I" ONLY

10-63-3064	5199-06	27.5	32.5	6
▲ -3054	▲ -05	22.5	27.5	5
▼ -3044	▼ -04	17.5	22.5	4
▼ -3034	▼ -03	12.5	17.5	3
10-63-3024	5199-02	7.5	12.5	2
EDP.NO.	ENG.NO.	B	(A)	極数 CKT.

REVISED EC NO: J2007-3407 DRWN:TKON 2007/06/20 CHKDM: SOGAYA 2007/06/25 APPR: THARUYAMA 2007/06/25	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE SPOX 5/7.5 PITCH REC HSG	
		10 UNDER	±0.2	DRAWN BY K. KOHAMA	DATE 2000/03/28	MOLEX INCORPORATED				
		10 OVER 30 UNDER	±0.25	CHECKED BY T. YAMAGUCHI	DATE 2000/03/30					
		30 OVER	±0.3	APPROVED BY M. FUKUSHIMA	DATE 2000/03/30					
		ANGULAR ±3 °		MATERIAL NO.						DOCUMENT NO.
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-5199-001			1 OF 1		
	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					