

Professionally approved products.

Datasheet

2 port VGA Video Splitter

RS Stock number [390-1423](#)



Features

- Compatible for use with VGA, SVGA and Multi-Sync Monitors.
- Duplicate one signal input to multiple outputs.
- Ability to be cascaded, increasing the total number of video outputs.
- Effective transmission distance: 65 Mtrs. (210ft)
- Automatic power-save when signal is lost.
- Clear Images.

Applications

These Video Splitters can be used for:

- Monitor Testing and Burn-in
- Business Meetings
- Demonstrations
- Trade Shows
- Exhibits

Professionally approved products.

Specifications

Depth	85mm
Device Type	Splitter
Dimensions	180 x 85 x 20mm
Height	20mm
Maximum Resolution	1920 x 1440pixels
Number of Ports	2
Video Connection Type	VGA
Weight	400g
Width	180mm
Number of Outputs	2
Signal Bandwidth	350 Mhz
Signal Type	VGA, SVGA, Multi-sync
Cable Length	65m
Connector – Input	HD15. Male x1
Connector – Output	HD15. Female x2
Enclosure	Metal