

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
HDIST
-


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		FIRST ISSUE	14MAY07	DC	TdB
A1		REVISED PER ECO-09-026495	NOV09	KK	AEG



NOTES:

- 1) CABLE DIAMETER 3 TO 11 MM DEPENDING ON PLACEMENT OF THE GROMMET.
2) MINIMUM ORDER QUANTITY FOR ALL PARTNUMBERS 100 KITS



3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI





9 POS




15 POS



25 POS



37 POS



D-SUBMINIATURE COVER KIT


PARTNUMBER	POSITION	THREAD JACKSCREW	COLOR
5-885000-1	9	#4-40 UNC	BLACK
5-885000-2	15	#4-40 UNC	BLACK
5-885000-3	25	#4-40 UNC	BLACK
5-885000-4	39	#4-40 UNC	BLACK
2-885000-1 3	9	M3	BLACK
2-885000-2 3	15	M3	BLACK
2-885000-3 3	25	M3	BLACK
2-885000-4 3	39	M3	BLACK

ITEM	QTY	DESCRIPTION	MATERIAL
1	1	COVER	NYLON 6 UL94V-2
2	2	JACKSCREW	NI PLATED BRASS
3	1	GROMMET	NYLON 6 UL94V-2
4	1	CABLE CLAMP	ZN PLATED STEEL
5	2	SELF TAPPING SCREW	ZN PLATED STEEL

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL

FINISH

DWN 14MAY07

D.CAMPSCHROER

CHK 14MAY07

D.CAMPSCHROER

APVD 14MAY07

T. DE BOER

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

tyco
Electronics

TYCO ELECTRONICS NEDERLAND B.V.

1's-HERTOGENBOSCH, THE NETHERLANDS

NAME

SUB-D COVER KIT; 9, 15, 25 OR 39 POS.
M3 OR #4-40 UNC TRHEADED JACKSCREW

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-

2-885000-1

RESTRICTED TO

-

SCALE NTS

SHEET

OF

REV A1