



ENGLISH

Datasheet

RS Pro Round Fixed Height Mount, 120mm, Rubber, Galvanised Steel 1000daN, M25

RS Stock No: **442-662**



Product Details

RS Pro round anti-vibration mount has rubber and galvanised steel construction for long life durability. It has a static load capacity of 1000 kg and thread size of M25. A series of machine mounts specially designed for free-standing applications in which heavy demand is required. Ideal for effective vibration damping and the reduction of noise emanating from machinery and other equipment. This pad mount can be used in applications that do not have bolt holes or, where bolt holes are inaccessible. It consists of a pressure plate coated in friction rubber that rests on a levelling bolt built-into a steel chassis and a thick rubber damping element. The design of the mount means that it can withstand most types of grease, acid, oil and coolants that are used in industry. This design has been tried and tested with excellent levelling results making it a natural choice for the majority of machine types used in industry today.

Features and Benefits

- Withstands heavy loads
- Effective vibration damping
- Noise reduction



ENGLISH

Specifications:

Foot Shape	Round
Material	Rubber
Metalwork	Galvanised Steel
Mounting Type	Screw-In
Type	Anti-Vibration Mount
Diameter	120 mm
Overall Height	77 mm
Static Load Capacity	1000 kg
Thread Size	M25