

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130091-0023](#)
Status: **Active**
Overview: [Electric Reels](#)
Description: Woodhead® Standard Cord Reel, 16/3 SJTOW Cord, 15.24m (50.0') Cord Length with 15A Pendant Outlet Box, Two Duplex, NEMA 5-15 Outlets

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR29921
 UL E22769

General

Product Family Electric Reels
 Series [130091](#)
 Cable Length 0.457m (1.50')
 Depth 0.30m (11.75")
 Duty Standard
 Enclosure Rating NEMA 1
 Height 0.36m (14.25")
 NEMA Configuration NEMA 5-15
 Overview [Electric Reels](#)
 Product Literature Order No 987650-8061
 Product Name Super-Safeway™
 Type Cord Reel
 UPC 78678833615
 Width 196.85mm (7.750")
 Woodhead Yes

Physical

Cable Movement Ratchet Lock
 Cord Length 15.24m (50.0')
 Drum Lock Ratchet
 Guide Arm 2 - Position
 Material - Coating Powder Coating
 Material - Housing Steel/Polycarbonate
 Mounting Style Rigid
 Net Weight 131.540/kg
 Number of Conductors 3
 Number of Receptacles 4
 Packaging Type Carton
 Primary Cord/Cable Entry N/A
 Retraction Weight 1.4kg (3.0 lb)
 Wire Size AWG 16

Electrical

Bulb Included N/A
 Cord Type 16/3 SJTOW
 Current - Maximum per Contact 8A
 GFCI No
 Lamp Type N/A
 Lamp Wattage - Maximum N/A
 On/Off Switch No
 Voltage - Maximum 120V



EU RoHS

Not RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130091Series](#)

Material Info

Old Part Number

980-3000

Reference - Drawing Numbers

Sales Drawing

SD-130091-006

This document was generated on 10/13/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION