







10 9 8 7 6 5 4 3 2 1



NOTES:

1. MATERIAL: PHOS BRONZE OR BRASS, SEE CHART
2. FINISH-1: PREPLATED OVERALL TIN: 0.00254/.000100 MIN
FINISH-2: SELECT GOLD: 0.00038/.000015 MIN OVER
0.00127/.000050 MIN NICKEL OVERALL
3. PRODUCT SPECIFICATION: PS-172160-0001
4. PACKAGING SPECIFICATION: PK-172160-0001
5. COSMETIC SPECIFICATION: PS-45499-0002 CLASS B
6. TERMINAL ACCEPTS WIRE AWG
18-20 AWG WIRE WITH 2.79/.110 MAX INSULATION DIA.
7. TERMINAL FOR USE WITH HOUSING 172159



MATERIAL NO	WIRE SIZE	MATERIAL	FINISH
172160-1802	18-20 AWG	PHOS BRONZE	SELECT GOLD
172160-1803	18-20 AWG	PHOS BRONZE	TIN
172160-1805	18-20 AWG	BRASS	SELECT GOLD
172160-1806	18-20 AWG	BRASS	TIN

ADD METRIC DIMS. EC NO: UCP2015-0951 DRAWN:MKIPPER 2014/09/03 CHKD:NGUYEN 2014/09/03 APPR:FSMITH 2014/09/10 REV	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 8:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY KSAMIEC	DATE 2013/08/23	TITLE EDGEMATE CRIMP TERMINALS 3.96/.156 CENTER FOR HOUSING 172159				
		4 PLACES	± ---	± ---	CHECKED BY	DATE					
		3 PLACES	± ---	± .010	APPROVED BY JCOMERC I		DATE 2013/11/14	DOCUMENT NO. molex SD-172160-0000			
		2 PLACES	± 0.25	± .015	MATERIAL NO.		SEE CHART				
		1 PLACE	± 0.38	± ---	ANGULAR ± 1/2°		SHEET NO. 1 OF 1				
		0 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						
D1	REV			SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

9 8 7 6 5 4 3 2 1