

miScroll Tablet

Data Sheet

Play, Watch, Listen, Browse, Personalise and Socialise with miScroll, the 7" touch-screen Android™ (2.3) tablet with interchangeable cover! miScroll is a fully-featured tablet that offers an expansive multimedia and social networking experience. Running on Android 2.3 and powered by a 1GHz ARM11 processor, miScroll is the perfect social networking companion, keeping you up to date and entertained on the go.



Express yourself anytime and anywhere, not only by changing your online status but also by changing miScroll's cover*. And don't worry about running out of power, miScroll's replaceable battery* means you can carry a spare and replace it on the go.

miScroll. Personalise. Socialise.

*Spare covers and battery available separately, visit www.storageoptions.com/miscroll

Features and Benefits

- Replaceable Battery
- Changeable Back Cover
- 7" Resistive Touch Screen
- HDMI Output Full HD 1080p
- USB Host Port
- Micro SD Card Slot
- Built-in Camera

Contents - Tablet PC, Power Adaptor, USB Cable, On The Go Cable, Earphones, Manual, Battery and Cover.

Part No. 52578



miScroll Tablet

Data Sheet



Software

- Android™ 2.3

Hardware

- Processor: 1GHz, ARM11
- Display: 7", 800x480, 16.9, Resistive Touch
- Memory: 256MB DDR2 RAM
- Internal Memory: 4GB Memory Built-in, Micro SD Card Expandable up to 32GB
- Battery: 9.25Wh High Capacity Battery, Removable (Available as an Accessory)
- Camera: Built-in, 0.3 Megapixel
- G-Sensor: 16 bit G-sensor, Monitors and Rotates Screen Through 360°
- Speaker: 1W/8Ω speaker



Connectivity

- Wireless Networking: Wi-Fi 802.11b/g
- Headphone: 3.5mm Earphone Jack
- TV Output: Mini HDMI Socket
Full 1080P When Connected to a Suitable HDTV
- USB Host Port: For Peripheral Connection (e.g. Keyboard, Flash Drive)

Multimedia

- 3D Support: OpenGL 2.0 3D support
- Video Support: Full 1080p, MPEG-2, MPEG-4, AVS, H.264, WMV, AVI, MP4, RMVB, FLV, MKV
- E-Book Support: EPUB, TXT, HTM, HTML, FB2

Features

- Music, Photos, Movies, E-mail, 3D Games

Case

- Plastic with Changeable Back Cover

Dimensions

- 200mm x 122mm x 12mm

