

Datasheet

RS Pro Mechanical HVAC Thermostat, RS Pro, RTRE6732, Fan Coil, Changeover 10 A, 2 A, 4 A, 5 A

RS Stock No: **375-0196**



Product Details

RS Pro changeover HVAC thermostat has a contact rating of 10 A, 2 A, 4 A and 5 A. This wall mountable, fan coil thermostat has a voltage rating of 230 V ac.

Features and Benefits

- Wall mounting
- Runs fans continuously when switched on and the thermostat controls the valve
- Cooling or heating operational modes



Specifications:

Contact Rating	10 A, 2 A, 4 A, 5 A
Maximum Temperature	+30°C
Minimum Temperature	+5°C
Supply Voltage	230 V ac
Switch Configuration	Changeover
Temperature Range	+5 to +30°C