

Datasheet

## RS Pro Right Angle 75Ω Cable Mount BNC Connector Plug, Clamp Termination URM 70

RS Stock No: **546-4386**



### Product Details

RS Pro right angle cable mount BNC connector plug features copper contacts. This male connector plug has 75 Ω impedance. It operates at a voltage rating of 335 V and temperature rating of -65 to +85°C.

### Features and Benefits

- Copper contacts
- Clamp termination method
- Male connector



ENGLISH

### Specifications:

Body Orientation	Right Angle
Cable Type	URM 70
Contact Material	Copper
Gender	Male
Impedance	75 $\Omega$
Mounting Type	Cable Mount
Polarity	Normal
Termination Method	Clamp
Standards Met	RoHS Compliant